




Belt-Drive Power Washer

Power Washers



UPC: 696471067125

Model G006712-1 (50-State & Canada)

UPC: 696471086690





FEATURES

POWER

 Powerful Generac® G-Force Engine delivers maximum cleaning performance and reliability. Low-oil shutdown protects the engine.

DURABILITY

- Heavy Duty Belt Drive Triplex Pump Up to 3X longer life than direct drive triplex pumps, re-buildable for easy maintenance.
- Stainless Steel Reinforced Hose Durable, non-marring hose will not leave scuff marks.

EASE OF USE

Brass Quick Change Fittings - For faster connections.

MOBILITY

- Compact Lightweight Design Up to 50 lbs. less weight vs. other belt-drive power washers.
- Oversized Pneumatic Wheels Easily handle rugged jobsite terrain.

COMFORT

 Ergonomic Spray Gun - Quick change connections, stabilizing side handle, molded grip, and easy-to-pull trigger for comfort during prolonged use.



3800 psi specifications

PRESSURE AND FLOW

Outlet Pressure (psi/bar)	3800/262
Flow Rate (gpm)/(L/min)	3.2/12.1

ENGINE

Manufacturer	Generac
Displacement (in ³ /cc)	18.4/302
Туре	OHV (Overhead Valve
Orientation	Horizontal
Low Oil Shutdown System	Yes
Fuel Capacity (gal/L)	1.7/6.4
Fuel On/Off Valve	Yes
Oil Capacity (oz/L)	37/1.1
Recommended Engine Oil	10W-30/SAE 30
Throttle Control	Manual
Choke	Manual
Starting Method	Manual/Recoil

PUMP

Туре	Triplex
Plunger	Ceramic-coated Stainless Steel
Maximum Water Supply Temperature (°F/°C)	100/38

HOSE

Length (ft/m)	50/15.2
Rating (psi/bar)	4000/276
Connectors	Quick Change

NOZZELS & DETERGENT

Number of Nozzles per Unit	5
Nozzle Descriptions	0, 15, 25, 40, Soap

GUN & LANCE

Gun	Professional
Gun to Lance Connection	M22 Threaded
Gun to Hose Connection	Quick Change
Lance Length (in/cm)	33/84.8
Lance to Nozzle Connection	Quick Change

FRAME & MISC.

Frame Construction	Steel
Wheels (in/cm)	4 x 10 / 10.1 x 25.4 Pneumatic

DIMENSIONS & WEIGHTS

Unit Length (in/cm)	35.5/90.2
Unit Width (wheel to wheel, in/cm)	25.25/53.3
Unit Height (in/cm)	26.75/67.9
Unit Weight (lbs/kg)	134/60.8
Boxed Length (in/cm)	37.5/82.5
Boxed Width (in/cm)	27/68.5
Boxed Height (in/cm)	32/81
Boxed Weight (lb/kg)	187/84.8

WARRANTY

Residential	3 year limited
Commercial / Rental	1 year limited

