



### **COMMERCIAL POWER WASHER** 4000 psi

Model and UPC



#### **FEATURES**

**POWERED** by

HONDA

- O POWER: The powerful Honda GX390 OHV engine delivers maximum cleaning performance and reliability. Low-oil shutdown protects the engine.
- O DURABILITY: Commercial Grade Direct Drive CAT® Triplex Pumps - Up to 4X longer life than axial cam pumps. The rugged frame is 1.25 in (31.8 mm) welded steel tube with a 12 gauge formed steel baseplate. The 35 ft (10.7 m) steel reinforced hose is durable and non-marring, so it will not leave scuff marks.
- C EASY-TO-USE: Save time with the easy-to-move 3-wheel design that moves with you around the jobsite to prevent downtime. Features an integrated 5 gal (18.9 L) bucket holder for detergent or onboard storage. Save space with the folding handle for compact storage and transport. The pressure control valve allows for adjustable cleaning power.

- **MOBILITY:** Oversized never-flat wheels easily handle rugged jobsite terrain.
- **COMFORT:** The ergonomic spray gun features quick change connections, a stabilizing side handle, a molded grip, and an easyto-pull trigger for comfort during prolonged use.

2 of 2

# GENERAC PRO

# **Specifications**

## PRESSURE AND FLOW

4000 psi

Maximum outlet pressure (psi / bar)	4,000 / 276
Maximum flow rate (gpm) / (L/min)	3.5 / 13.2

#### **ENGINE**

Manufacturer	Honda
Displacement (in <sup>3</sup> / cc)	23.7 / 389
Туре	4 cycle / OHV
Orientation	Horizontal
Lubrication method	Splash
Low oil shutdown system	Yes
Fuel capacity (gal / L)	1.52 / 5.8
Fuel ON/OFF valve	Yes
Oil capacity (oz / L)	37 / 1.1
Recommended engine oil	10W-30/SAE 30
Throttle control	Manual
Choke	Manual
Starting method	Manual/recoil

#### **PUMP**

Туре	Triplex
Manufacturer	CAT
Plunger	Ceramic
Maximum water supply temperature (°F / °C)	100 / 38
Warranty	5 year limited

#### HOSE

Туре	Polyurethane, steel braided
Length (ft / m)	35.0 / 10.7
Diameter (in / mm)	0.38 / 9.5
Rating (psi / bar)	4,200 / 290
Connectors	Quick change

#### **DETERGENT SYSTEM**

Chemical tank	No
Chemical tank description	5 gal (18.9 L) detergent bucket holder

#### **NOZZELS & DETERGENT**

Number of nozzles per unit	5
Nozzle descriptions	0°, 15°, 25°, 40°, Soap

#### **GUN & LANCE**

Gun type	Professional
Gun to lance connection	M22
Gun to hose connection	Quick connect
Lance length (in / cm)	29 / 74
Lance material	Stainless steel
Lance to nozzle connection	Quick connect

#### FRAME & MISC.

Handle	Folding
Frame construction	1.25 in (31.8 mm) welded tube steel
Wheels (in / mm)	3 x 10 (76.2 x 254) Never Flat

#### **DIMENSIONS & WEIGHTS**

Storage unit length (in / cm)	38.1 / 96.8
Extended unit length (in / cm)	51.5 / 130.9
Unit width (wheel to wheel, in / cm)	23.3 / 59.2
Storage unit height (in / cm)	27.6 / 70.1
Extended unit height (in / cm)	32.5 / 82.5
Unit weight (lbs / kg)	150 / 68.0
Boxed length (in / cm)	40.0 / 101.6
Boxed width (in / cm)	27.0 / 68.6
Boxed height (in / cm)	32.8 / 83.3
Boxed weight (lb / kg)	186 / 84.4

#### WARRANTY

Commercial (unit)	3 year limited
-------------------	----------------

