

OneWASH™

Power Washers

2000-3100 psi - Model 006602-0 (49-State & Canada)
UPC: 696471066029



*Built in the USA using domestic and foreign parts

FEATURES

POWERDIAL™ VARIABLE PRESSURE CONTROL

- Adjust the spray intensity to meet a wide-variety of cleaning tasks

POWERFUL 212cc GENERAC OHV ENGINE

- Delivers maximum cleaning performance and reliability

CONSOLIDATED CONTROL PANEL

- All controls are efficiently located in a single location

AXIAL CAM PUMP WITH EASY-ACCESS HOSE CONNECTIONS

- Prevents kneeling down on the ground

DRAINABLE DETERGENT TANK

- Allows for easy cleaning of the tank after each use

OVERSIZED NEVER-FLAT TIRES

- Improved mobility on rugged terrain

30' HIGH PRESSURE HOSE

- Extended range for improved use

2000-3100 psi

specifications

PRESSURE AND FLOW

Max Outlet Pressure (psi/bar)	3100/214
Max Flow Rate (gpm)/(L/min)	2.8/10.6

ENGINE

Manufacturer	Generac
Displacement (in ³ /cc)	12.9/212
Type	OHV (Overhead Valve)
Orientation	Horizontal
Low Oil Shutdown System	No
Fuel Capacity (gal/L)	0.8/3
Fuel On/Off Switch	Yes
Oil Capacity (oz/L)	20/0.6
Recommended Engine Oil	SAE 30 or 10W30
Throttle Control	PowerDial™ / Manual
Choke	Manual
Starting Method	Manual/Recoil

PUMP

Type	Axial Cam
Maximum Water Supply Temperature (°F/°C)	100/38

HOSE

Length (ft/m)	30/9.1
Rating (psi/bar)	3100/214
Connectors	M22 threaded

NOZZLES & DETERGENT

Number of Nozzles per Unit	3
Nozzle Descriptions	0, 25, soap
Chemical Tank Capacity (gal/L)	.75/2.8

GUN & LANCE

Gun Type	Ergonomic - 3100 psi
Gun to Lance Connection	M22 Threaded
Gun to Hose Connection	M22 Threaded
Lance Length (in/cm)	20/51
Lance to Nozzle Connection	Quick Change

FRAME & MISC.

Handle	Folding
Frame Construction	Welded Steel
Wheels (in/cm)	2.5 x 11 / 6.4 x 27.9 Never flat

DIMENSIONS & WEIGHTS

Unit Length (in/cm)	20.6/52.3
Unit Width (wheel to wheel, in/cm)	21/53.3
Unit Height (in/cm)	39.5/100.3
Unit Weight (lbs/kg)	68.5/31.1
Boxed Length (in/cm)	22.5/57.2
Boxed Width (in/cm)	22.5/57.2
Boxed Height (in/cm)	22.5/57.2
Boxed Weight (lbs/kg)	75/34

WARRANTY

Warranty	2 year limited
----------	----------------