

## GUARDIAN<sup>®</sup> SERIES Residential Standby Generators Air-Cooled Gas Engine

#### 1 of 6

### INCLUDES:

● True Power™ Electrical Technology

16/20/22 kW

- Two-line multilingual digital LCD Evolution<sup>™</sup> controller (English/Spanish/French/Portuguese)
- Two transfer switch options available: 100 amp, 16 circuit switch or 200 amp service rated smart switch
- Electronic governor
- Standard Wi-Fi<sup>™</sup> connectivity available on 16kW and 20kW -1 models and 22kW models
- System status & maintenance interval LED indicators
- Sound attenuated enclosure
- Flexible fuel line connector
- Natural gas or LP gas operation
- 5 Year limited warranty
- Listed and labeled by the Southwest Research Institute allowing installation as close as 18 in (457 mm) to a structure.\*
  \*Must be located away from doors, windows, and fresh air intakes and in accordance with local codes. https://assets.swri.org/library/DirectoryOfListedProducts/ ConstructionIndustry/973 DoC 204 13204-01-01 Rev9.pdf

### Standby Power Rating

G007035-1, G007036-1, G007037-1 (Aluminum - Bisque) - 16 kW 60 Hz G007038-1, G007039-1 (Aluminum - Bisque) - 20 kW 60 Hz G007042-10, G007043-10 (Aluminum - Bisque) - 22 kW 60 Hz



Product shown with optional fascia kit



Note: CETL or CUL certification only applies to unbundled units and units packaged with limited circuit switches. Units packaged with the Smart Switch are ETL or UL certified in the USA only.

### FEATURES

- INNOVATIVE ENGINE DESIGN & RIGOROUS TESTING are at the heart of Generac's success in providing the most reliable generators possible. Generac's G-Force engine lineup offers added peace of mind and reliability for when it's needed the most. The G-Force series engines are purpose built and designed to handle the rigors of extended run times in high temperatures and extreme operating conditions.
- O TRUE POWER™ ELECTRICAL TECHNOLOGY: Superior harmonics and sine wave form produce less than 5% Total Harmonic Distortion for utility quality power. This allows confident operation of sensitive electronic equipment and micro-chip based appliances, such as variable speed HVAC systems.
- TEST CRITERIA:
  - ✓ PROTOTYPE TESTED
    - SYSTEM TORSIONAL TESTED
- NEMA MG1-22 EVALUATION MOTOR STARTING ABILITY
- MOBILE LINK<sup>®</sup> CONNECTIVITY: FREE with select Guardian Series Home standby generators, Mobile Link Wi-Fi allows users to monitor the status of the generator from anywhere in the world using a smartphone, tablet, or PC. Easily access information such as the current operating status and maintenance alerts. Users can connect an account to an authorized service dealer for fast, friendly, and proactive service. With Mobile Link, users are taken care of before the next power outage.

1

- SOLID-STATE, FREQUENCY COMPENSATED VOLTAGE REGULATION: This state-of-the-art power maximizing regulation system is standard on all Generac models. It provides optimized FAST RESPONSE to changing load conditions and MAXI-MUM MOTOR STARTING CAPABILITY by electronically torque-matching the surge loads to the engine. Digital voltage regulation at ±1%.
- SINGLE SOURCE SERVICE RESPONSE from Generac's extensive dealer network provides parts and service know-how for the entire unit, from the engine to the smallest electronic component.
- GENERAC TRANSFER SWITCHES: Long life and reliability are synonymous with GENERAC POWER SYSTEMS. One reason for this confidence is that the GENERAC product line is offered with its own transfer systems and controls for total system compatibility.



2 of 6

# 16/20/22 kW

#### Engine

- Generac G-Force design
- "Spiny-lok" cast iron cylinder walls
- Electronic ignition/spark advance
- Full pressure lubrication system
- Low oil pressure shutdown system
- High temperature shutdown

#### Generator

- Revolving field
- Skewed stator
- Displaced phase excitation
- Automatic voltage regulation
- EPA Certified for non-emergency applications
- UL 2200 listed

#### Transfer Switch (if applicable)

- Fully automatic
- NEMA 3R
- Remote mounting

#### **Evolution™ Controls**

- AUTO/MANUAL/OFF illuminated buttons
- Two-line multilingual LCD
- Sealed, raised buttons
- Utility voltage sensing
- Generator voltage sensing
- Utility interrupt delay
- Engine warm-up
- Engine cool-down
- Programmable exercise
- Smart battery charger
- Main line circuit breaker
- Electronic governor

#### Unit

- SAE weather protective enclosure
- Enclosed critical grade muffler
- Small, compact, attractive

Produces a smooth output waveform for compatibility with electronic equipment. Maximizes motor starting capability.

Maximizes engine "breathing" for increased fuel efficiency. Plateau honed cylinder walls and plasma moly

Pressurized lubrication to all vital bearings means better performance, less maintenance, and longer engine

Allows for a smaller, light weight unit that operates 25% more efficiently than a revolving armature generator.

rings help the engine run cooler, reducing oil consumption and resulting in longer engine life.

Regulating output voltage to  $\pm 1\%$  prevents damaging voltage spikes.

Rigid construction and added durability provide long engine life.

life. Now featuring up to a 2 year/200 hour oil change interval.

Prevents damage due to overheating.

These features combine to assure smooth, quick starting every time.

Shutdown protection prevents catastrophic engine damage due to low oil.

Allows unit to be used for demand response applications (applicable to 22 kW units).

For your safety.

Transfers vital electrical loads to the energized source of power.

Can be installed inside or outside for maximum flexibility.

Mounts near an existing distribution panel for simple, low-cost installation.

Selects the operating mode and provides easy, at-a-glance status indication in any condition. Provides homeowners easily visible logs of history, maintenance, and events up to 50 occurrences.

Smooth, weather-resistant user interface for programming and operations.

Constantly monitors utility voltage, setpoints 65% dropout, 80% pick-up, of standard voltage.

Constantly monitors generator voltage to verify the cleanest power delivered to the home.

Prevents nuisance start-ups of the engine, adjustable 2-1500 seconds from the factory default setting of 5 seconds by a qualified dealer.

- Verifies engine is ready to assume the load, setpoint approximately 5 seconds.
- Allows engine to cool prior to shutdown, setpoint approximately 1 minute.

Operates engine to prevent oil seal drying and damage between power outages by running the generator for 5 minutes every other week. Also offers a selectable setting for weekly or monthly operation providing flexibility and potentially lower fuel costs to the owner.

Delivers charge to the battery only when needed at varying rates depending on outdoor air temperature. Compatible with lead acid and AGM-style batteries.

Protects generator from overload.

Maintains constant 60 Hz frequency.

Sound attenuated enclosures ensure quiet operation and protection against mother nature, withstanding winds up to 150 mph (241 km/h). Hinged key locking roof panel for security. Lift-out front for easy access to all routine maintenance items. Electrostatically applied textured epoxy paint for added durability.

 $\label{eq:Quiet, critical grade muffler} \ensuremath{\mathsf{Q}}\xspace{\ensuremath{\mathsf{u}}\xspace{\ensuremath{u}\xspace{\ensuremath{\mathsf{u}}\xspace{\ensur$ 

Makes for an easy, eye appealing installation, as close as 18 in (457 mm) away from a structure.



### **Features and Benefits**

# GENERAC

**Features and Benefits** 

### 16/20/22 kW

#### **Installation System**

- 14 in (35.6 cm) flexible fuel line connector
- Integral sediment trap

#### Connectivity (Wi-Fi equipped models only)

- Ability to view generator status
- Ability to view generator Exercise/Run and Total Hours
- Ability to view generator maintenance information
- Monthly report with previous month's activity
- Ability to view generator battery information
- Weather information

- Listed ANSI Z21.75/CSA 6.27 outdoor appliance connector for the required connection to the gas supply piping.
- Meets IFGC and NFPA 54 installation requirements.
- Monitor generator with a smartphone, tablet, or computer at any time via the Mobile Link application for complete peace of mind.
- Review the generator's complete protection profile for exercise hours and total hours.
- Provides maintenance information for the specific model generator when scheduled maintenance is due.
- Detailed monthly reports provide historical generator information.
  - Built in battery diagnostics displaying current state of the battery.
  - Provides detailed local ambient weather conditions for generator location.

3 of 6

4 of 6

## 16/20/22 kW

# GENERAC

### **Specifications**

Generator			<b></b>
Model	16 kW	20 kW	22 kW
Rated maximum continuous power capacity (LP)	16,000 Watts*	20,000 Watts*	22,000 Watts*
lated maximum continuous power capacity (NG)	16,000 Watts*	18,000 Watts*	19,500 Watts*
lated voltage	240	240	240
lated maximum continuous load current – 240 volts (LP/NG)	66.7 / 66.7	83.3 / 75.0	91.7 / 81.3
otal Harmonic Distortion	70	Less than 5%	400
Aain line circuit breaker	70 amp	90 amp	100 amp
hase		1	
lumber of rotor poles		2	
lated AC frequency		60 Hz	
lower factor		1.0	
attery requirement (not included)	· · · · · ·	540 CCA minimum or Group 35AG	
Jnit weight (Ib / kg)	409 / 186	448 / 203	466 / 211
Vimensions (L x W x H) in / cm		48 x 25 x 29 / 121.9 x 63.5 x 73.7	
Sound output in dB(A) at 23 ft (7 m) with generator operating at normal load**	67	67	67
ound output in dB(A) at 23 ft (7 m) with generator in Quiet-Test™ low-speed exercise mode**	55	55	57
xercise duration		5 min	
Engine			
ngine type		GENERAC G-Force 1000 Series	
Number of cylinders		2	
Displacement		999 cc	
Cylinder block		Aluminum w/ cast iron sleeve	
'alve arrangement		Overhead valve	
qnition system		Solid-state w/ magneto	
Governor system		Electronic	
Compression ratio		9.5:1	
Starter		12 VDC	
Dil capacity including filter		Approx. 1.9 qt / 1.8 L	
Deprating rpm		3.600	
Fuel consumption		0,000	
latural gas ft <sup>3</sup> /hr (m <sup>3</sup> /hr)			
1/2 Load	218 (6.17)	204 (5.78)	228 (6.46)
Full Load	309 (8.75)	301 (8.52)	327 (9.26)
.iquid propane ft <sup>3</sup> /hr (gal/hr) [L/hr]	74 (2.03) [7.70]	87 (2.37) [8.99]	92 (2.53) [9.57]
1/2 Load Full Load	107 (2.94) [11.11]	130 (3.56) [13.48]	142 (3.90) [14.77]
Note: Fuel pipe must be sized for full load. Required fuel pressure to generator fuel inlet at all load rang			
For BTU content, multiply ft <sup>3</sup> /hr x 2500 (LP) or ft <sup>3</sup> /hr x 1000 (NG). For Megajoule content, multiply m <sup>3</sup> /hr			
Controls			
wo-line plain text multilingual LCD	Sim	ple user interface for ease of opera	tion
Mode buttons: AUTO		· ·	
MANUAL		atic start on utility failure. 7 day exe	
OFF		ol, unit stays on. If utility fails, trans	
	Stops unit. Po	wer is removed. Control and charge	er still operate.
Ready to Run/Maintenance messages		Standard	
ingine run hours indication	0	Standard	1.5
Programmable start delay between 2–1500 seconds	Sta	andard (programmable by dealer or	lly)
Jtility Voltage Loss/Return to Utility adjustable (brownout setting)		From 140-171 V / 190-216 V	
uture Set Capable Exerciser/Exercise Set Error warning		Standard	
Run/Alarm/Maintenance logs		50 events each	
ngine start sequence		ig: 16 sec on, 7 rest (90 sec maxin	,
Starter lock-out	Starter canno	t re-engage until 5 sec after engine	has stopped.
Smart Battery Charger		Standard	
Charger Fault/Missing AC warning	Standard		
ow Battery/Battery Problem Protection and Battery Condition indication	Standard		
utomatic Voltage Regulation with Over and Under Voltage Protection		Standard	
Inder-Frequency/Overload/Stepper Overcurrent Protection		Standard	
Safety Fused/Fuse Problem Protection		Standard	
Automatic Low Oil Pressure/High Oil Temperature Shutdown		Standard	
)vercrank/Overspeed (@ 72 Hz)/rpm Sense Loss Shutdown		Standard	
ligh Engine Temperature Shutdown		Standard	
nternal Fault/Incorrect Wiring protection		Standard	
Common external fault capability		Standard	
ield upgradable firmware		Standard	
Pating definitions — Optional Standby: Applicable for supplying backup power for the duration of the utility			

Rating definitions - Optional Standby: Applicable for supplying backup power for the duration of the utility power outage with correct maintenance performed. No overload capability is available for this rating. (All ratings in accordance with BS5514, IS03046, UL2200, and DIN6271). \* Maximum kilovolt amps and current are subject to and limited by such factors as fuel BTU/megajoule content, ambient temperature, altitude, engine power and condition, etc. Maximum power decreases approximately 3.5% for each 1,000 ft (304.8 m) above sea level; and also will decrease approximately 1% for each 10 °F (6 °C) above 60 °F (16 °C). \* \*Sound levels are taken from the front of the generator. Sound levels taken from other sides of the generator may be higher depending on installation parameters.

### 16/20/22 kW

#### **Limited Circuits Switch Features**

- 16 space, 24 circuit, breakers not included.
- Electrically operated, mechanically-held contacts for fast, positive connections.
- Rated for all classes of load, 100% equipment rated, both inductive and resistive.
- 2-pole, 250 VAC contactors.
- 30 millisecond transfer time.
- Dual coil design.
- Rated for both copper and aluminum conductors.
- Main contacts are silver plated or silver alloy to resist welding and sticking.
- NEMA/UL 3R aluminum outdoor enclosure allows for indoor or outdoor mounting flexibility.
- Multi listed for use with 1 in standard, tandem, GFCI and AFCI breakers from Siemens, Murray, Eaton, and Square D for the most flexible and cost effective install.

### Dimensions

	Height		Height Width		Donth
	H1	H2	W1	W2	Depth
in	26.75	30.1	10.5	13.5	6.91
cm	67.95	76.45	26.67	34.29	17.55

	Wire Ranges	
Conductor Lug	Neutral Lug	Ground Lug
1/0 - #14	2/0 - #14	2/0 - #14

#### **Service Rated Smart Switch Features**

- Includes digital power management technology (DPM) standard.
- Intelligently manages up to four air conditioner loads with no additional hardware.
- Up to eight additional large (240 VAC) loads can be managed when used in conjunction with Smart Management Modules (SMMs).
- Electrically operated, mechanically-held contacts for fast, clean connections.
- Rated for all classes of load, 100% equipment rated, both inductive and resistive.
- 2-pole, 250 VAC contactors.
- Service equipment rated, dual coil design.
- Rated for both aluminum and copper conductors.
- Main contacts are silver plated or silver alloy to resist welding and sticking.
- NEMA/UL 3R aluminum outdoor enclosure allows for indoor or outdoor mounting flexibility.

### Dimensions

	Height		Height Width		Dopth
	H1	H2	W1	W2	Depth
in	26.75	30.1	10.5	13.5	6.91
cm	67.95	76.45	26.67	34.29	17.55

Wire Ranges		
Conductor Lug	Neutral Lug	Ground Lug
350 MCM - #6	350 MCM - #6	2/0 - #14

Switch Options
G007036 (16kW)
2
100


GENERA

100
120 / 240, 1Ø
80% 65%
Approx. 15 sec
Standard
Standard
24
8 tandems
10,000

\*Function of Evolution controller Exercise can be set to weekly or monthly


Model

No. of poles



Model	G007037 (16 kW) / G007039 (20 kW) / G007043 (22 kW)
No. of poles	2
Current rating (amps)	200
Voltage rating (VAC)	120/240, 1Ø
Utility voltage monitor (fixed)* <i>-Pick-up</i> -Dropout	80% 65%
Return to Utility*	Approx. 13 sec
Exercises bi-weekly for 5 minutes*	Standard
ETL or UL listed	Standard
Enclosure type	NEMA/UL 3R
Circuit breaker protected	22,000
Lug range	250 MCM - #6
*Function of Evolution controller	

Exercise can be set to weekly or monthly



# GENERAC


## 16/20/22 kW

6 of 6

Model #	Product	Description
G005819-0	26R Wet Cell Battery	Every standby generator requires a battery to start the system. Generac offers the recommended 26R wet cell battery for use with all air-cooled standby product (excluding PowerPact <sup>™</sup> ).
G007101-0	Battery Pad Warmer	Pad warmer rests under the battery. Recommended for use if temperature regularly falls below 0 °F (-18 °C). (Not nec- essary for use with AGM-style batteries).
G007102-0	Oil Warmer	Oil warmer slips directly over the oil filter. Recommended for use if temperature regularly falls below 0 °F (-18 °C).
G007103-1	Breather Warmer	Breather warmer is for use in extreme cold weather applications. For use with Evolution controllers only in climates where heavy icing occurs.
G005621-0	Auxiliary Transfer Switch Contact Kit	The auxiliary transfer switch contact kit allows the transfer switch to lock out a single large electrical load that may not be needed. Not compatible with 50 amp pre-wired switches.
G007027-0 - Bisque	Fascia Base Wrap Kit	The fascia base wrap snaps together around the bottom of the new air-cooled generators. This offers a sleek, contoured appearance as well as offering protection from rodents and insects by covering the lifting holes located in the base.
G005703-0 - Bisque	Touch-Up Paint Kit	If the generator enclosure is scratched or damaged, it is important to touch up the paint to protect from future corrosion. The touch-up paint kit includes the necessary paint to correctly maintain or touch up a generator enclosure.
G006485-0	Scheduled Maintenance Kit	Generac's scheduled maintenance kit provides all the items necessary to perform complete routine maintenance on a Generac automatic standby generator (oil not included).
G007005-0	Wi-Fi LP Tank Fuel Level Monitor	The Wi-Fi enabled LP tank fuel level monitor provides constant monitoring of the connected LP fuel tank. Monitoring the LP tank's fuel level is an important step in verifying the generator is ready to run during an unexpected power failure. Status alerts are available through a free application to notify users when the LP tank is in need of a refill.
G007000-0 (50 amp) G007006-0 (100 amp)	Smart Management Module	Smart Management Modules (SMM) are used to optimize the performance of a standby generator. They manage large electrical loads upon startup and shed them to aid in recovery when overloaded. In many cases, using SMM's can reduce the overall size and cost of the system.
G007169-0	Mobile Link <sup>®</sup> 4G LTE Cellular Accessory	The Mobile Link 4G LTE Cellular Accessory allows users to monitor the status of the generator from anywhere in the world, using a smart phone, tablet, or PC. Easily access information such as the current operating status and maintenance alerts. Users can connect an account with an authorized service dealer for fast, friendly, and proactive service. With Mobile Link, users are taken care of before the next power outage.
G007220-0 - Bisque	Base Plug Kit	Base plugs snap into the lifting holes on the base of air-cooled home standby generators. This offers a sleek, contoured appearance, as well as offers protection from rodents and insects by covering the lifting holes located in the base. Kit contains four plugs, sufficient for use on a single air-cooled home standby generator.

### **Dimensions & UPCs**

Model	UPC
G007035	696471074161
G007036	696471074154
G007037	696471074178
G007038	696471074185
G007039	696471074192
G007042	696471074208
G007043	696471074215



Dimensions shown are approximate. See installation manual for exact dimensions. DO NOT USE THESE DIMENSIONS FOR INSTALLATION PURPOSES.

